



RAMI, Inc.
Grand Haven, MI 49417
(616) 842-9450
www.rami.com

AV-928 Antenna Diplexer (Incomplete System)

Diplexer Ports

| | |
|-------------|--|
| ANT | to AV-925 Antenna or other suitable broad band antenna |
| 136-174 MHz | to 136-174 MHz transceiver antenna connector |
| 760-870 MHz | to 760-870 MHz transceiver antenna connector |

Installation Instructions

The AV-928 requires use of RG-400 (or similar) 50 ohm transmission lines and male type BNC connectors (not supplied).

Determine suitable mounting location, drill mounting holes utilizing “mounting template” supplied and secure diplexer via mounting tabs (mounting hardware not supplied).

Route, secure and attach transmission lines from transceiver and antenna to appropriate ports on diplexer.

