



RAMI, Inc.
Grand Haven, MI 49417
(616) 842-9450
www.rami.com

AV-930 Antenna Diplexer (Incomplete System)

Diplexer Ports

ANT	to AV-925 Antenna or other suitable broad band antenna
136-174 MHz	to 136-174 MHz transceiver antenna connector
380-870 MHz	to 380-870 MHz transceiver antenna connector

Installation Instructions

The AV-930 requires use of RG-400 (or similar) 50 ohm transmission lines and male type TNC connectors (not supplied).

Determine suitable mounting location, drill mounting holes utilizing “mounting template” supplied and secure diplexer via mounting tabs (mounting hardware not supplied).

Route, secure and attach transmission lines from transceiver and antenna to appropriate ports on diplexer.

