



RAMI, Inc.
Grand Haven, MI 49417
(616) 842-9450
www.rami.com

AV-929 Antenna Diplexer (Incomplete System)

Diplexer Ports

ANT	to AV-925 Antenna or other suitable broad band antenna
380-520 MHz	to 380-520 MHz transceiver antenna connector
760-870 MHz	to 760-870 MHz transceiver antenna connector

Installation Instructions

The AV-929 requires use of RG-400 (or similar) 50 ohm transmission lines and male type BNC connectors (not supplied).

Determine suitable mounting location, drill mounting holes utilizing “mounting template” supplied and secure diplexer via mounting tabs (mounting hardware not supplied).

Route, secure and attach transmission lines from transceiver and AV-925 antenna to appropriate ports on diplexer.

