



RAMI, Inc.
Grand Haven, MI 49417
(616) 842-9450
www.rami.com

AV-931 Antenna Diplexer (Incomplete System)

Diplexer Ports

ANT	to AV-925 Antenna or other suitable broad band antenna
150-174 MHz	to 150-174 MHz transceiver antenna connector
118-137 MHz	to 118-137 MHz transceiver antenna connector

Installation Instructions

The AV-931 requires use of RG-400 (or similar) 50 ohm transmission lines and male type BNC connectors (not supplied).

Determine suitable mounting location, drill mounting holes utilizing “mounting template” supplied and secure diplexer via mounting tabs (mounting hardware not supplied).

Route, secure and attach transmission lines from transceiver and AV-925 antenna to appropriate ports on diplexer.

